


Safelights for Darkrooms



Bright illumination safelights for X-ray film processing darkrooms

Features

- ▶ Deliver high brightness for both indirect and direct illumination of the darkroom
- ▶ Provide continuous brightness adjustment, enabling film processing without danger of causing fog
- ▶ Include a bracket for wall or ceiling mounting

The yellow safelight is supplied with a 25 W krypton lamp in combination with a Schott filter glass. Only yellow light is emitted, fulfilling the requirements for blue sensitive X-ray films used with or without intensifying screens.

The red safelight is supplied with a 40 W krypton lamp and a homogenous Schott filter glass. This combination emits red light only to comply with the requirements for green sensitive X-ray films and other high sensitivity films, which must be handled with red light only.

Ordering Information

Darkroom safelight 230 V, yellow for blue sensitive X-ray films:

T50001.1.010 with bracket for wall or ceiling mounting
L379005 Spare lamp 25 W for yellow safelight

Darkroom safelight 230 V, red for green sensitive X-ray films:

T5418/U10 with bracket for wall or ceiling mounting
L379004 Spare lamp 40 W for red safelight